


Sieve rotation holder SRH 4/200 with integrated rotation

for Elma ultrasonic cleaning units



- time & moneysaving yet intensive cleaning of analytical sieves
- simultaneous cleaning of up to 4 sieves at once (diam: 200mm)
- sieves from different producer's can be cleaned at the same time



- simple to operate, no installation required
- usable on old transonic and new Elmasonic cleaning units
- made from hygienic and easy to clean stainless steel



- tilted position allows thorough and even cleaning with additional rinsing effect
- dirt and contaminants collect on bottom of tank, not in other sieves
- no damage to sieves; web tension and mesh size are not affected by ultrasonic cleaning



www.elma-germany.com

Technical Data SRH 4/200

Power (Vac)	230 / 110 V
Supply Frequency (Hz)	50 / 60
Outer dimensions w / d / h (mm)	580 / 260 / 300
Weight (ca. kg)	5,75
Made from	Stainless Steel

Elma Accessory

Order Number

SRH 4/200 230 V	100 9133
SRH 4/200 115 V	100 9145

Useable for following Elma Ultrasonic Models

Order Number

Elmasonic S 300 H - 230 V Elmasonic S 300 H - 115 V	(for one SRH 4/200)*	100 3033 100 7158
Elmasonic S 300 - 230 V Elmasonic S 300 - 115 V	(for one SRH 4/200)*	100 4669 100 7157
Elmasonic S 450 H - 230 V Elmasonic S 450 H - 2x115 V (for USA)	(for one SRH 4/200)*	100 3908
Elmasonic S 900 H - 230 V Elmasonic S 900 H - 2x115 V (for USA)	(for two SRH 4/200)*	100 3946
Trasonic T 890 - 230 V Trasonic T 890 - 115 V	(for one SRH 4/200)*	298 400 0000 298 400 0003
Trasonic T 890/H - 230 V Trasonic T 890/H - 115 V	(for one SRH 4/200)*	298 400 2000 298 400 2003
Trasonic T 1040 H - 230 V Trasonic T 1040 H - 115 V	(for one SRH 4/200)*	298 600 0000 298 600 2003
Trasonic T 1060 H - 230 V Trasonic T 1060 H - 2x115 V (for USA)	(for two SRH 4/200)*	298 650 0000

* not included in order number for Elma ultrasonic model, please order separately

